

760154112 | H61A-318-BLUE

High Density Icon Strip, blue, bulk pack



OBSOLETE

Replaced By:

760164426
H61K-ICON-BL

HGS620 Icon Strip (Voice / Data / Blank), Blue (25 ea/pkg)

Product Classification

| | |
|------------------------------|---------------------------------------------------------------------|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Icon kit |
| Ordering Note | Minimum order quantity, 20 packs |

General Specifications

Color Blue

Dimensions

Height 13.97 mm | 0.55 in

Width 23.62 mm | 0.93 in

Depth 2.79 mm | 0.11 in

Material Specifications

Material Type High-impact, flame retardant, thermoplastic

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

760154112 | H61A-318-BLUE

Flammability Rating UL 94 V-0

Safety Standard UL | cUL

Packaging and Weights

Packaging quantity 25

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--------------------------------------------------------------------------------------------------------------------------------|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

