



SS Type Label Card Sheet for Metal Faceplates

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Label kit

General Specifications

ANSI/TIA Category 3 | 5 | 5e | 6 | 6A

Application Compatible with M11SP-L, M12SP-L, M13SP-L, M14SP-L, M16SP-L, M28SP-L, M12S-L-TRS1 faceplates

Color White

Mounting Snap-in

Dimensions

Height 279.4 mm | 11 in

Width 215.9 mm | 8.5 in

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Safety Standard UL | cUL

Packaging and Weights

Included Ten sheets, 180 labels per sheet

Packaging quantity 1

Weight, net 0.136 kg | 0.3 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

REACH-SVHC

Classification

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance