



High-Density Front-Loading Cable Manager Shallow, 4U

- Offers bend radius and mechanical protection
- Rubber entry/exit retainers ensure cable captivity preventing accidental disturbance of patch cords
- Suitable for Twisted Pair and Fiber Optic patch cords

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Cable management hardware
Minimum Order Quantity	4
Ordering Note	Sold per piece with an MOQ of 4 pieces

General Specifications

Color	Black
Rack Units	4

Dimensions

Height	177.8 mm   7 in
Width	63.5 mm   2.5 in
Depth	98.044 mm   3.86 in

Material Specifications

Finish	Smooth
Material Type	Galvanized steel   PA   TPE

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Flammability Rating	UL 94 V-0
Safety Standard	UL   cUL

Packaging and Weights

Packaging quantity	1
--------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant

