

E20® Empty Conduit, 12.7 mm/10 mm, Riser, light yellow



- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	North America
Product Type	Empty conduit
Product Brand	E#O®
Government Funding	Build America Buy America (BABA) compliant*
Warranty	One year

General Specifications

Color	Light yellow
Conduit Type	Non-toneable
Density, maximum	0.946 g/cm ³ 0.034 lb/in ³
Density, minimum	0.943 g/cm ³ 0.034 lb/in ³
Design Standard	ASTM D3350-05
Wall Type	Ribbed

Dimensions

Inner Diameter, nominal	9.804 mm 0.386 in
Outer Diameter, nominal	12.7 mm 0.5 in
Wall Thickness, minimum	1.346 mm 0.053 in
Nominal Size	12.7 mm

Material Specifications

Material Type	HDPE base + FR additive
----------------------	-------------------------

Mechanical Specifications

Minimum Bend Radius, unsupported	330.2 mm 13 in
---	------------------

360000014

Tensile Strength at yield, minimum 20.684 N/mm² | 3000 psi
Pulling Tension, maximum 78.018 kg | 172 lb

Environmental Specifications

Flame Test Listing UL 2024

Packaging and Weights

Weight, net 62.503 kg/km | 42 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Warranty For more information, please consult our Product Warranty guidelines