# 460159095 | OCC1P-10400-NNNQSEB



OCC1P Wideband Splitter, planar, singlemode, 1x4, symmetrical ratio, 0.250/0,9 mm cable, medium duty housing

### **Product Classification**

Regional Availability EMEA | Latin America | North America

Product Type Splitter component

Product Series OCC1P

## General Specifications

**Device Type** Component, rectangular

**Functionality** Splitting

**Technology Type** Planar lightwave circuit (PLC)

**Application** For use in FOSC closures

Circuits, quantity 1

**Distribution Type** 1 x 4 splitter

Interface, InputStub tailInterface, OutputStub tail

Split Ratio Symmetrical

Splitter, quantity 1

#### Dimensions

Pigtail Length, Input
2.5 m | 8.202 ft

Pigtail Length, Output
2.5 m | 8.202 ft

Pigtail Diameter, Input
0.25 mm | 0.01 in

Pigtail Diameter, Output
0.25 mm | 0.01 in

### **Environmental Specifications**



# 460159095 | OCC1P-10400-NNNQSEB

Qualification Standards Telcordia GR-1209-CORE | Telcordia GR-1221-CORE

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

