# 460159107 | OCC1A-1230-NNANQNA-TAP

OCC1A Wideband Splitter, singlemode, 1x2, 70/30 ratio, 0.250 mm cable, light duty housing



#### **Product Classification**

Regional Availability North America

Product Type Splitter component

Product Series OCC1A

### General Specifications

**Device Type** Component, tubular

**Functionality** Splitting

**Technology Type** Fused biconic tapered

**Application** For use in FOSC closures

Circuits, quantity

**Distribution Type** 1 x 2 splitter

Interface, InputStub tailInterface, OutputStub tailSplit Ratio70/30

Splitter, quantity 1

#### **Dimensions**

Pigtail Length, Input2.5 m | 8.202 ftPigtail Length, Output2.5 m | 8.202 ftPigtail Diameter, Input0.25 mm | 0.01 inPigtail Diameter, Output0.25 mm | 0.01 in

## Packaging and Weights



# 460159107 | OCC1A-1230-NNANQNA-TAP

#### **Packaging quantity**

1

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

