# 460159111 | OCC1A-1207-NNANQNA-TAP

OCC1A Wideband Splitter, singlemode, 1x2, 93/7 ratio, 0.250 mm cable, light duty housing



#### **Product Classification**

Regional Availability North America

Product Type Splitter component

Product Series OCC1A

### General Specifications

**Device Type** Component, tubular

**Functionality** Splitting

**Technology Type** Fused biconic tapered

**Application** For use in FOSC closures

Circuits, quantity 1

**Distribution Type** 1 x 2 splitter

Interface, InputStub tailInterface, OutputStub tailSplit Ratio97/3

Splitter, quantity 1

#### **Dimensions**

Pigtail Length, Input
2.5 m | 8.202 ft

Pigtail Length, Output
2.5 m | 8.202 ft

Pigtail Diameter, Input
0.25 mm | 0.01 in

Pigtail Diameter, Output
0.25 mm | 0.01 in

### Packaging and Weights



# 460159111 | OCC1A-1207-NNANQNA-TAP

#### **Packaging quantity**

1

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

