626298-000 | OCC1A-1245-NNANQNF

OCC1A Wideband Splitter, singlemode, 1x2, 55/45 ratio, 0.250 mm cable, field installable



Product Classification

Regional Availability	North America		
Product Type	Splitter component		
Product Series	OCC1A		

General Specifications

Device Type	Component, tubular	
Functionality	Splitting	
Technology Type	Fused biconic tapered	
Application	For use in FOSC closures	
Circuits, quantity	1	
Distribution Type	1 x 2 splitter	
Interface, Input	Stub tail	
Interface, Output	Stub tail	
Split Ratio	55/45	
Splitter, quantity	1	

Dimensions

Pigtail Length, Input	2.5 m 8.202 ft
Pigtail Length, Output	2.5 m 8.202 ft
Pigtail Diameter, Input	0.25 mm 0.01 in
Pigtail Diameter, Output	0.25 mm 0.01 in

Packaging and Weights

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 20, 2023



626298-000 | OCC1A-1245-NNANQNF

Packaging quantity

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

1

REACH-SVHC

ROHS



UK-ROHS

Below maximum concentration value
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant
Compliant

Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 20, 2023

