## 7803298 | SFP+, 10GBase CWDM-370, up to 40 km



Small form factor pluggable+ Module, 10G BASE, CWDM, Singlemode

## **Product Classification**

Product Type Optical module

Product Series SFP+

General Specifications

Interface LC/UPC

Note Detailed Product Specifications are available. Please contact your local CommScope

representative.

**Dimensions** 

 Height
 12 mm | 0.472 in

 Width
 14 mm | 0.551 in

 Depth
 57 mm | 2.244 in

**Optical Specifications** 

**Fiber Type** 9/125 μm, singlemode

Average Optical Output Power, maximum6 dBmAverage Optical Output Power, minimum1 dBm

**Rx/Tx Power Accuracy**  $\pm 3 dB / \pm 3 dB$ 

**Operating Wavelength** 1260 – 1610 nm (Rx) | 1370 nm

Receiver Sensitivity, maximum -14.4 dBm

Receiver Overload +1 dBm

**Environmental Specifications** 

**Operating Temperature**  $0 \,^{\circ}\text{C}$  to +70  $^{\circ}\text{C}$  (+32  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

Packaging and Weights

**Height, packed** 20 mm | 0.787 in

Page 1 of 2

## 7803298 | SFP+, 10GBase CWDM-370, up to 40 km

 Width, packed
 105 mm | 4.134 in

 Depth, packed
 65 mm | 2.559 in

Packaging quantity 1

Packaging Type Box

 Weight, gross
 0.036 kg | 0.079 lb

 Weight, net
 0.022 kg | 0.049 lb