CT-30-TUW-43-I6



30 dB, Tapper, 340 – 6000 MHz

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Tapper

General Specifications

Device Type Tapper

Application Indoor/Outdoor

Color White Inner Contact Plating Silver

Interface 4.3-10 Female

Outer Contact Plating Trimetal

Dimensions

 Height
 25 mm | 0.984 in

 Width
 43 mm | 1.693 in

 Length
 141 mm | 5.551 in

Electrical Specifications

3rd Order IMD -165 dBc

3rd Order IMD Test Method Two +43 dBm carriers

Insertion Loss at Frequency Band 0.15 dB @ 1695-2700 MHz | 0.15 dB @ 340-960 MHz | 0.2 dB @ 3500-4500

MHz | 0.2 dB @ 4900-6000 MHz

Return Loss at Frequency Band 19.1 dB @ 3500-4500 MHz | 19.1 dB @ 4900-6000 MHz | 20.8 dB @ 1695-2700

MHz | 20.8 dB @ 340-960 MHz

Average Power, maximum 300 W

Coupling 30 dB

Coupling Tolerance +1.5/-0.2dB @ 698-960 MHz | +1.7/-0.3dB @ 340-698 MHz | +1/-2.5dB @ 4900-6000

MHz | +2.7/-0.5dB @ 3500-4500 MHz | ±1dB @ 1695-2700 MHz

Impedance 50 ohm

Page 1 of 2

CT-30-TUW-43-16

Operating Frequency Band 1695 – 2700 MHz | 340 – 960 MHz | 3500 – 4500 MHz | 4900 – 6000 MHz

Peak Power, maximum3 kWReflected Power, maximum200 W

Mechanical Specifications

Coupling Nut Proof Torque 7 N-m | 61.955 in lb

Environmental Specifications

Operating Temperature $-35 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-31 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Relative Humidity Up to 100%

Corrosion Test Method IEC 60068-2-11, 30 days
Ingress Protection Test Method IEC 60529:2001, IP67

Packaging and Weights

 Height, packed
 40 mm | 1.575 in

 Width, packed
 90 mm | 3.543 in

 Length, packed
 180 mm | 7.087 in

 Weight, gross
 300 g | 0.661 lb

 Weight, net
 250 g | 0.551 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

UK-ROHS Compliant/Exempted





