

# 760249308 | CPP-IP-6A-STP-1U-24



## CommScope® imVision® STP Cat 6A Modular Panel, 24 port

### Product Classification

<b>Regional Availability</b>	Asia   EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	RJ45 patch panel
<b>Product Brand</b>	imVision®

### General Specifications

<b>ANSI/TIA Category</b>	6A
<b>Cable Type</b>	Shielded
<b>Color</b>	Silver
<b>Intelligence Type</b>	iPatch® enabled
<b>Panel Style</b>	Straight
<b>Rack Units</b>	1
<b>Total Ports, quantity</b>	24
<b>Wiring</b>	T568A   T568B

### Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	206.5 mm   8.13 in
<b>Compatible Diameter Over Dielectric, maximum</b>	1.168 mm   0.046 in

### Electrical Specifications

<b>Current Rating at Temperature</b>	1.5 A @ 20 °C   1.5 A @ 68 °F
<b>Dielectric Withstand Voltage, RMS, conductive surface</b>	1,500 Vac @ 60 Hz
<b>Insulation Resistance, minimum</b>	500 MOhm

### Mechanical Specifications

# 760249308 | CPP-IP-6A-STP-1U-24

---

**Plug Insertion Life, minimum**

750 times

## Environmental Specifications

**Operating Temperature**

-10 °C to +60 °C (+14 °F to +140 °F)

**Storage Temperature**

-40 °C to +70 °C (-40 °F to +158 °F)

**Safety Standard**

UL | cUL

## Packaging and Weights

**Packaging quantity**

1

## Regulatory Compliance/Certifications

**Agency**

**Classification**

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

