

# E80815-000 | OCAB-D4-15-B3-01



Fiber Optic Power Reducing Build Out Attenuator, singlemode D4/UPC, 15dB

- Designed to reduce or balance the power in passive optical networks
- Insertable between the connector and the adapter and therefore suited for distribution frames, cabinets and boxes
- High system flexibility because of wave-length independency and polarization insensitivity

## OBSOLETE

This product was discontinued on: April 5, 2022

## Product Classification

<b>Regional Availability</b>	EMEA   Latin America   North America
<b>Product Type</b>	Fiber attenuator
<b>Product Series</b>	OCAB

## General Specifications

<b>Interface</b>	D4/UPC
------------------	--------

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	G.652.D
<b>Attenuation Tolerance</b>	± 10%
<b>Attenuation, nominal</b>	15 dB
<b>Operating Wavelength</b>	1260 – 1360 nm
<b>Optical Power, maximum</b>	250 mW
<b>Return Loss, minimum</b>	45 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Storage Temperature</b>	-40 °C to +80 °C (-40 °F to +176 °F)

## Regulatory Compliance/Certifications

**Agency****Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

