

#### High-Density Front-Loading Cable Manager, 4U

- Offers bend radius and mechanical protection
- Suitable for Twisted Pair and Fiber Optic patch cords
- Rubber entry/exit retainers ensure cable captivity preventing accidental disturbance of patch cords

#### **Product Classification**

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

**Product Type** Cable management hardware

Minimum Order Quantity 4

Ordering Note Sold per piece with an MOQ of 4 pieces

## General Specifications

Color Black
Rack Units 4

#### **Dimensions**

 Height
 177.8 mm | 7 in

 Width
 63.5 mm | 2.5 in

**Depth** 150.114 mm | 5.91 in

## Material Specifications

**Finish** Smooth

Material Type Galvanized steel | PA | TPE

## **Environmental Specifications**

**Operating Temperature**  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

Flammability Rating UL 94 V-0
Safety Standard UL | cUL

## Packaging and Weights

Packaging quantity 1

Page 1 of 2

# 1671495-4

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



