

TeraSPEED® LC UniBoot 1.5MM LC/UPC UNIBOOT DUPLEX CONNECTOR

OBSOLETE

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber connector
Product Brand	SYSTIMAX ULL TeraSPEED®
Product Series	Uniboot

General Specifications

Body Style	Duplex
Color	Blue
Interface	LC/UPC
Interface Feature	Uniboot

Dimensions

Compatible Cable Diameter	1.5 mm 0.059 in
----------------------------------	-------------------

Material Specifications

Ferrule Material	Zirconia
-------------------------	----------

Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0° 4.40 lb @ 90°
--	-------------------------------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.652.D G.657.A2 OS2
Insertion Loss Change, mating	0.25 dB
Optical Components Standard	ANSI/TIA-568-C.3
Insertion Loss, ULL, maximum	0.25 dB
Insertion Loss, ULL, typical	0.2 dB

860650411

Return Loss, minimum 50 dB

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



* Footnotes

Insertion Loss Change, mating TIA-568: Maximum insertion loss change after 500 matings