# FGS-MSHS-F



#### FiberGuide® Horizontal Straight Section, 4x12in, Yellow

#### **Product Classification**

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Straight section
Product Brand FiberGuide®

Product Series FGS

### General Specifications

**Color** Yellow

**Orientation** Horizontal

Section Type Straight section

#### **Dimensions**

 Height
 102 mm | 4.016 in

 Width
 347 mm | 13.661 in

 Length
 1829 mm | 72.008 in

**System Dimensions** 102 mm x 305 mm (4 in x 12 in)

#### Material Specifications

Material Type Engineering Thermoplastic

## **Environmental Specifications**

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0
Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

## Packaging and Weights

**Weight, net** 5.208 kg | 11.482 lb

**COMMSCOPE®** 

# FGS-MSHS-F

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

