

F2A-HRHR-P

FSJ2-50 SureFlex® Jumper with interface types 4.3-10 Male Right Angle and 4.3-10 Male Right Angle.



Product Classification

Product Type	Wireless transmission cable assembly
Product Brand	HELIAX® SureFlex®
Product Series	FSJ2-50

General Specifications

Body Style, Connector A	Right angle
Body Style, Connector B	Right angle
Interface, Connector A	4.3-10 Male
Interface, Connector B	4.3-10 Male
Specification Sheet Revision Level	A

Dimensions

Length	0.914 m 2.999 ft
Nominal Size	3/8 in

Electrical Specifications

3rd Order IMD Dynamic	-118 dBm
3rd Order IMD Dynamic Test Method	Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.196	20.99
1700–2700 MHz	1.196	20.99

Jumper Assembly Sample Label

F2A-HRHR-P



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition