M61-ACC

Base Product



MGS Icon Strip (Voice / Data / Blank)

Product Classification

Portfolio SYSTIMAX®

Product Type Icon kit

Material Specifications

Material Type High-impact, flame retardant, thermoplastic

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \text{ (-40 }^{\circ}\text{F to } +158 \,^{\circ}\text{F)}$

Flammability Rating UL 94 V-0

Safety Standard UL | cUL