## CX2455-000 | OCC1P-16400-S3SESEB



OCC1P Wideband Splitter, planar, singlemode, 1x64, symmetrical split ratio, SC/APC 9°, 0.9 mm cable, medium duty housing

### **Product Classification**

Regional Availability EMEA | Latin America | North America

Product Type Splitter component

Product Series OCC1P

## General Specifications

**Device Type** Component, rectangular

**Functionality** Splitting

**Technology Type** Planar lightwave circuit (PLC)

**Application** For use in FOSC closures

Circuits, quantity

**Distribution Type** 1 x 64 splitter

Interface, InputSC/APCInterface, OutputSC/APC

Split Ratio Symmetrical

Splitter, quantity 1

#### **Dimensions**

Pigtail Length, Input1.5 m | 4.921 ftPigtail Length, Output1.5 m | 4.921 ftPigtail Diameter, Input0.9 mm | 0.035 inPigtail Diameter, Output0.9 mm | 0.035 in

### **Environmental Specifications**



# CX2455-000 | OCC1P-16400-S3SESEB

**Qualification Standards** Telcordia GR-1209-CORE | Telcordia GR-1221-CORE

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

