# CZ8590-000 | OCC1P-23200-NNNQNQF

OCC1P Wideband Splitter, planar, singlemode, 2x32, symmetrical split ratio, 0,250 mm cable, field installable

## Product Classification

1X32 Grade P 090063286

Regional Availability	EMEA   Latin America   North America
Product Type	Splitter component
Product Series	OCC1P

### **General Specifications**

Device Type	Component, rectangular
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Application	For use in FOSC closures
Circuits, quantity	1
Distribution Type	2 x 32 splitter
Interface, Input	Stub tail
Interface, Output	Stub tail
Split Ratio	Symmetrical
Splitter, quantity	1

#### Dimensions

Pigtail Length, Input	2.5 m   8.202 ft
Pigtail Length, Output	2.5 m   8.202 ft
Pigtail Diameter, Input	0.25 mm   0.01 in
Pigtail Diameter, Output	0.25 mm   0.01 in

# Environmental Specifications

Page 1 of 2

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or <sup>™</sup> are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: February 14, 2022



#### CZ8590-000 | OCC1P-23200-NNNQNQF

**Qualification Standards** 

Telcordia GR-1209-CORE | Telcordia GR-1221-CORE

## Packaging and Weights

Packaging quantity

## Regulatory Compliance/Certifications

1

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

Page 2 of 2

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: February 14, 2022

