



CWST wraparound repair sleeve heat shrink kit, unpressurized, for 15 to 75 mm cable diameter, 1000 mm long

- Excellent split resistance of the composite structure offers superior resistance to mechanical abuse during and after the installation
- Integrated moisture barrier completely reconstitutes the cable sheath construction

OBSOLETE

This product was discontinued on: April 15, 2020

Product Classification

Regional Availability	EMEA
Product Type	Heat shrink repair sleeve
Product Series	CWST

General Specifications

Color	Black
Sealant Type	Hotmelt adhesive

Dimensions

Length	1000 mm 39.37 in
Expanded Inside Diameter, minimum	75 mm 2.953 in
Recovered Inside Diameter, maximum	15 mm 0.591 in
Single Cable Diameter, maximum	75 mm 2.953 in
Single Cable Diameter, minimum	15 mm 0.591 in
Expanded Wall Thickness, minimum	1.1 mm 0.043 in

Material Specifications

Material Type	Fiber-reinforced multi-layer sealing sleeve
----------------------	---------------------------------------------

Environmental Specifications

Environmental Space	Aerial Buried Ducted
----------------------------	--------------------------

Packaging and Weights

Packaging quantity 1
Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

