

Cushion Insert with 1 hole for HELIAX® cables (Fusion tape included)

## **Product Classification**

Product Type Cushion insert

Product Brand I-Line

Ordering Note CommScope® non-standard product

General Specifications

Cable TypeHybrid fiber

Cables per Cushion 1

**Color** Black

**Dimensions** 

**Height** 82.55 mm | 3.25 in

**Length** 25.4 mm | 1 in

Nominal Size 1-1/4 in

Material Specifications

Material Type EPDM rubber

**Environmental Specifications** 

UV Resistance Test Method MIL-STD-810E, Procedure 11, Method 505

**UV Resistance, minimum with no degradation** ≥1000 hours

Weather Resistance Test Method 04AS00-03.9.0 | IEC 60529:2001, IP66

Packaging and Weights

**Height, packed** 170.18 mm | 6.7 in

COMMSCOPE®

## 294701-T

**Width, packed** 129.54 mm | 5.1 in

**Length, packed** 99.06 mm | 3.9 in

**Included** Cushion

Packaging quantity

**Weight, gross** 0.5 kg | 1.102 lb

## Regulatory Compliance/Certifications

Agency Classification

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

## Included Products

FT-TB - Black Self-fusing Tape, 15 ft

