

Cushion Insert with 1 hole for 15/8 in corrugated coaxial cable

Product Classification

Product Type Cushion insert

Product Brand I-Line

Ordering Note CommScope® non-standard product

General Specifications

Cable Type Corrugated

Cables per Cushion 1

Color Black

Dimensions

Height 82.55 mm | 3.25 in

Length 25.4 mm | 1 in

Nominal Size 1-5/8 in

Material Specifications

Material Type EPDM rubber

Environmental Specifications

UV Resistance Test Method MIL-STD-810E, Procedure 11, Method 505

UV Resistance, minimum with no degradation ≥1000 hours

Weather Resistance Test Method 04AS00-03.9.0 | IEC 60529:2001, IP66

Packaging and Weights

Height, packed 170.18 mm | 6.7 in

COMMSCOPE®

294702

Width, packed 129.54 mm | 5.1 in

Length, packed 99.06 mm | 3.9 in

Included Cushion

Packaging quantity

Weight, gross 0.5 kg | 1.102 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

