381745-000 | FOSC-OC-6DSD1284NN

X

FOSC® A-TRAY-24 type, DWDM, 16 channels, demux, 1554.94 nm starting wavelength, 100 GHz channel spacing + upgrade

Product Classification

Regional Availability North America

Product Type DWDM splice tray

Product Brand FOSC®
Product Series FOSC-OC

General Specifications

Application For use in FOSC closures

Interface, InputStub tailInterface, OutputStub tail

Dimensions

 Height
 233.68 mm | 9.2 in

 Width
 99.06 mm | 3.9 in

 Depth
 10.67 mm | 0.42 in

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant



381745-000 | FOSC-OC-6DSD1284NN



