
386415-000 | FOSC-OC-3DGX1504NN2T-U23



FOSC® D-TRAY-72 type, DWDM, 12 channels, double demux, 1537.40 nm starting wavelength, 100 GHz channel spacing + upgrade

Product Classification

Regional AvailabilityNorth AmericaProduct TypeDWDM splice tray

Product Brand FOSC®
Product Series FOSC-OC

General Specifications

Application For use in FOSC closures

Interface, InputStub tailInterface, OutputStub tail

Dimensions

 Height
 375.92 mm | 14.8 in

 Width
 152.4 mm | 6 in

 Depth
 10.67 mm | 0.42 in

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

 Agency
 Classification

 CHINA-ROHS
 Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

COMMSC PE°

386415-000 | FOSC-OC-3DGX1504NN2T-U23



