760237723 | FOSC-OC-6DQD1214NN2T-U23

FOSC® A-TRAY-24 type, DWDM, 40 channels, demux, 1560.61 nm starting wavelength, 100 GHz channel spacing + upgrade

Product Classification

Regional Availability North America

Product Type DWDM splice tray

Product Brand FOSC®
Product Series FOSC-OC

General Specifications

Application For use in FOSC closures

Interface, InputStub tailInterface, OutputStub tail

Dimensions

 Height
 9.2 mm | 0.362 in

 Depth
 10.67 mm | 0.42 in

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted



