760242102 | FIST-FDASA2-AY1361NN-R



FIST® Fiber Splice Tray with Field Installable DWDM, 4 Channels and upgrade port, Double Multiplexing, 1548.52nm starting wavelength, 100GHz channel spacing, all fibers at right side

Product Classification

Regional Availability EMEA

Product Type DWDM splice tray

Product Brand FIST®

Product Series FIST-FDASA2

General Specifications

Application For use with FIST fiber splice closures | For use with FIST panels

Interface, InputStub tailInterface, OutputStub tail

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency	Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant



