
834892-000 | FOSC-OC-3DAX129ANN



FOSC® D-TRAY-72 type, DWDM, 4 channels + upgrade port, double demux, 1554.13 nm starting wavelength, skipped channel spacing

Product Classification

Regional AvailabilityNorth AmericaProduct TypeDWDM splice tray

Product Brand FOSC®
Product Series FOSC-OC

General Specifications

Application For use in FOSC closures

Interface, InputStub tailInterface, OutputStub tail

Dimensions

Agency

 Height
 375.92 mm | 14.8 in

 Width
 152.4 mm | 6 in

 Depth
 10.67 mm | 0.42 in

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

/ igolioy	
CHINA-ROHS	Below maximum concentration value

Classification

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

COMMSC PE®

834892-000 | FOSC-OC-3DAX129ANN



