

# 244106A-48

---



## Flex-Twist Hanger Assembly for WR187

### Product Classification

**Product Type** Hanger kit

### General Specifications

**Cable Type** Elliptical waveguide

**Cables per Hanger** 1

**Color** Silver

**Hanger Type** Flex-Twist hanger

**Mounting** 4.5 in OD pipe

### Dimensions

**Height** 387.4 mm | 15.252 in

**Width** 82.6 mm | 3.252 in

**Length** 387.4 mm | 15.252 in

**Waveguide Size** WR187 | WG12 | R48

### Material Specifications

**Material Type** Stainless steel

### Mechanical Specifications

**Wind Speed, survival with 1/2 in (12 mm) radial ice** 201.167 km/h | 125 mph

### Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Corrosion Test Method** MIL-F-14072C | MIL-STD-889B

# 244106A-48

---

## Packaging and Weights

<b>Included</b>	Clamp   Rubber grommet   Threaded rod
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	0.68 kg   1.499 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

