## AB-S50



Pipe-to-Pipe Adapter, adapts 1-1/2 in to 3-1/2 in OD pipe to 2-3/8 in to 5 in OD pipe

#### **Product Classification**

Product Type Adapter

General Specifications

MountingPipe-to-pipeTower TaperNon-tapered

**Dimensions** 

 Height
 50.8 mm | 2 in

 Width
 203.2 mm | 8 in

 Length
 304.8 mm | 12 in

 Mounting Diameter 2, maximum
 127 mm | 5 in

 Mounting Diameter 2, minimum
 60.96 mm | 2.4 in

 Mounting Diameter, maximum
 88.9 mm | 3.5 in

 Mounting Diameter, minimum
 38.1 mm | 1.5 in

Material Specifications

Material Type Hot dip galvanized steel

#### Packaging and Weights

Included Clamp halves | Threaded rod

Packaging quantity 2

**Weight, net** 8.2 kg | 18.078 lb

### Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

**COMMSCOPE®** 

# AB-S50



