



GSIC Weatherproofing Gel Sealed In-line Transition Boot, 1/2 inch to 1/4 inch cable

- Gel-sealed weatherproofing boots for sealing coaxial cable connection points providing an efficient moisture block
- Wraparound design eliminates the need to disconnect the connectors before installation
- No tape, no mastics or tools required for installation and removal

OBSOLETE

Product Classification

Regional Availability	Asia EMEA
Product Type	Weatherproofing boot
Product Series	GSIC

General Specifications

Application	1/2" Jumper to 1 1/4" Feeder
Color	Black

Dimensions

Length	187 mm 7.362 in
Cable Diameter for Seal, maximum	17 mm 0.669 in 40 mm 1.575 in
Cable Diameter for Seal, minimum	13 mm 0.512 in 38 mm 1.496 in
Inner Diameter	56 mm 2.205 in

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Weatherproofing Method	IP68

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

