

CC-100



Crossover Clamp, joins two 1-1/2 in to 2-1/2 in OD round members

Product Classification

Product Type Clamp set

General Specifications

Mounting Crossover clamp

Tower Taper Non-tapered

Dimensions

Height 127 mm | 5 in

Width 127 mm | 5 in

Length 127 mm | 5 in

Mounting Diameter, maximum 63.5 mm | 2.5 in

Mounting Diameter, minimum 38.1 mm | 1.5 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Clamp halves | Threaded rod

Packaging quantity 1

Weight, net 2.7 kg | 5.952 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

CC-100

