

# CW2311-000 | FIST-FCASA2-1R490NN-L



FIST® Fiber Splice Tray with Field Installable CWDM, 1 Channel, Add /drop for 2 fibers, 1491nm starting wavelength, all fibers at left side

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	CWDM splice tray
<b>Product Brand</b>	FIST®
<b>Product Series</b>	FIST-FCASA2

## General Specifications

<b>Application</b>	For use with FIST fiber splice closures   For use with FIST panels
<b>Interface, Input</b>	Stub tail
<b>Interface, Output</b>	Stub tail

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

