

# E45575-000 | FOSC-OC-6A11200

---

FOSC® A-TRAY-24 type with one 1x2 FBT splitter with symmetrical split ratio



## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Splitter splice tray
<b>Product Brand</b>	FOSC®
<b>Product Series</b>	FOSC-OC

## General Specifications

<b>Application</b>	For use in FOSC closures
<b>Interface, Input</b>	Stub tail
<b>Interface, Output</b>	Stub tail

## Dimensions

<b>Height</b>	10.67 mm   0.42 in
<b>Width</b>	99.06 mm   3.9 in

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

