

L5SGRIP



Support Hoisting Grip with clamp for 1.0-1.24 in (25.4-31.5 mm) coaxial cable

Product Classification

Product Type	Hoisting grip
Product Brand	HELIAX®
Ordering Note	ANDREW® standard product (Global)

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Hoisting Grip Type	Support hoisting grip
Installation Tool	Required, not included
Support Clamp	Included
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	431.8 mm 17 in
Leader Length, minimum	330.2 mm 13 in
Compatible Diameter, maximum	31.5 mm 1.24 in
Compatible Diameter, minimum	25.4 mm 1 in
Nominal Size	7/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

Pull Load Capacity	226.796 kg 500 lb
---------------------------	---------------------

L5SGRIP

Packaging and Weights

Packaging quantity	1
Weight, gross	0.33 kg 0.728 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system