

# LS-100-SSH

---



Tapered Pipe-to-Pipe Adapter, adapts 1-1/2 into 3-1/2 in OD pipe to 8 in to 16 in

## Product Classification

**Product Type** Adapter

## General Specifications

**Mounting** Pipe-to-pipe

**Taper Taper** Tapered

## Dimensions

**Height** 50.8 mm | 2 in

**Width** 304.8 mm | 12 in

**Length** 406.4 mm | 16 in

**Mounting Diameter 2, maximum** 406.4 mm | 16 in

**Mounting Diameter 2, minimum** 203.2 mm | 8 in

**Mounting Diameter, maximum** 88.9 mm | 3.5 in

**Mounting Diameter, minimum** 38.1 mm | 1.5 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Packaging and Weights

**Included** Clamp halves | Threaded rod

**Packaging quantity** 2

**Weight, net** 25 kg | 55.115 lb

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system

# LS-100-SSH

---

