PG-CS08



PIM-Guard Antenna and RRU Cable Support Bracket with 8 ports for stackable hangers (up to 3 per port). Install with torque wrench set at 10 to 15 ft-lb to meet carrier PIM requirements. For patents, see www.cs-pat.com

Product Classification

Product Type Support bracket
Product Brand PIM-Guard

General Specifications

Cable Runs, quantity 8
Hole, quantity 8

Mounting Pipe, 60.3–114.3 mm (2-3/8 in to 4-1/2 in) OD

Dimensions

 Height
 55.88 mm | 2.2 in

 Width
 248.92 mm | 9.8 in

 Length
 317.5 mm | 12.5 in

 Mounting Diameter, maximum
 60.96 mm | 2.4 in

 Mounting Diameter, minimum
 114.3 mm | 4.5 in

 Hole Size
 3/4 in | 7/16 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Packaging quantity 1

Weight, net 4.1 kg | 9.039 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

COMMSCOPE®

PG-CS08

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant





