760248043 | OCAB-P-S4-01-IGR-D315xW535



Inground-root for the 72f cabinet, depth 315mm, including mounting hardware

Product Classification

Regional Availability EMEA

Product Type Fiber cross-connect hub

Product Series OCAB

General Specifications

Color Light Gray (RAL 7035)

Mounting Cabinet

Dimensions

 Height
 280 mm | 11.024 in

 Width
 535 mm | 21.063 in

 Depth
 314.5 mm | 12.382 in

Enclosure Size Small

Material Specifications

Finish Powder coated polyester

Material Type Stainless steel grade 1.4003, 1.5 mm gauge, welded construction

Environmental Specifications

Environmental Space Outdoor, buried

Qualification Standards IK10

Packaging and Weights

Included Mounting hardware

Packaging quantity 8

Packaging Type Pallet

COMMSC PE®