



Inground-root for the 72f cabinet, depth 250mm, including mounting hardware

Product Classification

Regional Availability	EMEA
Product Type	Fiber cross-connect hub
Product Series	OCAB

General Specifications

Color	Light Gray (RAL 7035)
Mounting	Cabinet

Dimensions

Height	280 mm 11.024 in
Width	535 mm 21.063 in
Depth	250 mm 9.843 in
Enclosure Size	Small

Material Specifications

Finish	Powder coated polyester
Material Type	Stainless steel grade 1.4003, 1.5 mm gauge, welded construction

Environmental Specifications

Environmental Space	Outdoor, buried
Qualification Standards	IK10

Packaging and Weights

Included	Mounting hardware
-----------------	-------------------

760250899 | OCAB-P-S4-01-IGR-D250xW535

Packaging quantity 8
Packaging Type Pallet