

LSF2-50 SureFlex® Jumper with interface types NEX10 Male and 7 /16DIN Male, 2m

Product Classification

Product Type SureFlex® Premium, static PIM

Product Brand HELIAX® | SureFlex®

Product Series LSF2-50

General Specifications

Body Style, Connector AStraightBody Style, Connector BStraightInterface, Connector ANEX10 MaleInterface, Connector B7-16 DIN Male

Specification Sheet Revision Level A

Dimensions

Length 2 m | 6.562 ft

Nominal Size 3/8 in

Electrical Specifications

3rd Order IMD -112 dBm

3rd Order IMD Test Method Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-960 MHz	1.065	30
1700-2200 MHz	1.083	28
2500-2700 MHz	1.106	26
3400-3800 MHz	1.222	20

Page 1 of 2



LS2-XMDM-2M-P

Jumper Assembly Sample Label



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency Classification

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Included Products

LS2DM-S2 – 7/16 Male for 3/8 in LSF2-50 cable, factory attached
LS2XM-P – NEX10 Male for 3/8 in LSF2-50 cable, factory attached

LSF2-50 - LSF2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket

(Not for Individual Sale - Jumpers only)

