

# SSH-78

---



## SnapStak® Hanger for 7/8 in coaxial cable

### Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	SnapStak®
<b>Ordering Note</b>	ANDREW® standard product (Global)

### General Specifications

<b>Cables per Hanger</b>	1
<b>Color</b>	Silver
<b>Hanger Type</b>	Snap-in hanger
<b>Mounting</b>	3/4 in drilled cable ladder

### Dimensions

<b>Maximum Stack Height</b>	3
<b>Height</b>	40.9 mm   1.61 in
<b>Width</b>	40.1 mm   1.579 in
<b>Length</b>	64 mm   2.52 in
<b>Compatible Cable Diameter Range</b>	26.7–31 mm
<b>Compatible Diameter, maximum</b>	31 mm   1.22 in
<b>Compatible Diameter, minimum</b>	26.7 mm   1.051 in
<b>Nominal Size</b>	7/8 in

### Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

### Material Specifications

<b>Material Type</b>	Stainless steel
----------------------	-----------------

# SSH-78

---

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Corrosion Resistance, minimum with no degradation** ≥500 hours in salt spray chamber

**Environmental Strength Capability** Double cable weight

## Packaging and Weights

**Height, packed** 15.6 cm | 6.142 in

**Width, packed** 14.8 cm | 5.827 in

**Length, packed** 10.8 cm | 4.252 in

**Packaging quantity** 10

**Weight, gross** 0.42 kg | 0.926 lb

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power