

WB-K0510-B



Saftey Grated Waveguide Bridge Kit, 4-3/4 in x 10 ft, with two 13 ft 4 in direct bural posts

Product Classification

Product Type Waveguide bridge kit

General Specifications

Application Direct burial

Cable Runs, quantity 6

Pipe, quantity 2

Dimensions

Height 4064 mm | 160 in

Width 127 mm | 5 in

Length 3048 mm | 120 in

Pipe Length 4,053.84 mm | 159.6 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Caps | Channel | Hardware | Posts | Support brackets | Trapeze

Packaging quantity 1

Weight, net 114.6 kg | 252.649 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value

WB-K0510-B

ROHS Compliant/Exempted

UK-ROHS Compliant/Exempted

