

FGS-FLEXV-C



FiberGuide® FlexVertical Trough, 2x2in, Yellow

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Drop kit
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Product Feature	Snap-together design
Angle/Bend Direction	30°
Color	Yellow
Orientation	Vertical
Section Type	Vertical section

Dimensions

Height	76.2 mm 3 in
Width	64.516 mm 2.54 in
Length	67.056 mm 2.64 in
System Dimensions	51 mm x 51 mm (2 in x 2 in)

Material Specifications

Material Type	Engineering Thermoplastic
----------------------	---------------------------

Environmental Specifications

Flammability Rating	CSA S143 UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel TCO '99 WEEE
Safety Standard	CSA UL

FGS-FLEXV-C

Packaging and Weights

Included	Hardware
Packaging quantity	1
Weight, net	0.027 kg 0.06 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

