



FST-T2 Flexible Service Terminal, 12f, 6 Port x 2 Fiber, 6 HMFOC Adapters (Jack/male/pinned), 2 fibers per adapter at drop side, Stub at feeder side, black, 1000 ft/304 m

- Flexible Service Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-terminated and environmentally sealed for use in optical drop cable deployments
- Flexible structure allowing installation in constrained spaces

Product Classification

Regional Availability	North America
Product Type	Access terminal, with multi-fiber port
Product Series	FST-T2
Minimum Order Quantity	1

General Specifications

Cable Type	Dielectric - Loose Tube
Cable, quantity	7
Distribution Type	6 ports
Drop Port Type	Hardened multi-fiber (HMFOC) adapter
Enclosure Color	Black
Mounting	Handhole Pedestal
Port Type	Hardened multi-fiber (HMFOC) jack, male/pinned
Port, quantity	6
Splitter, quantity	0
Stub Type	Stub tail

Dimensions

Height	112.5 mm 4.429 in
Width	53 mm 2.087 in
Depth	31 mm 1.22 in
Cable Length, stub	1000 ft (304 m)
Cable Outer Diameter	4.1 x 7.6 mm (0.16 x 0.30 in)

Packaging quantity	1
Packaging Type	Box Carton
Weight, without cable	0.23 kg 0.507 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

