

# SRC3-U4K2B1BE000



NOVUX™ Specialty Range Closure 100, splice/patch, 1x LC/APC duplex adapter, 2x LC/APC Grade B 900µm pigtail, no splitters, 12 splices, SMOUV® 45mm splice protectors, black, NO splitter, 2x NVX-CR-TI-SM-NN cable retention

- Modern drop solution offering providers the agility and flexibility to use it in last-mile fiber network applications, both above and below ground
- Protected from harsh conditions by CommScope's Octopus gel sealing technology
- Agnostic to connectivity technologies: splice, connector, field-installable connector for agility and flexibility
- Identification plate for either QR code or customer logo
- QR code and CommScope cTrak® app for one-click access to all product information

## Product Classification

<b>Regional Availability</b>	Asia   EMEA   Latin America   North America
<b>Regional Availability Note</b>	Contact your local CommScope representative for specific availability
<b>Product Type</b>	Single-ended, rectangular fiber closure
<b>Product Brand</b>	NOVUX™
<b>Product Series</b>	SRC100

## General Specifications

<b>Cable Capacity, Drop</b>	4 Flat 8.0 x 4.5 mm (0.30 x 0.17 in)   4 Round 1.2–8.0 mm (0.05–0.31 in)
<b>Cable Ports Quantity, total</b>	4 multi-out ports (8 cables)
<b>Cable Sealing Type</b>	Compressed gel
<b>Cable Termination Attachments, quantity</b>	2
<b>Closure Sealing Type</b>	Hinged with latch
<b>Closure Style</b>	Single-ended
<b>Color</b>	Black
<b>Mounting</b>	Handhole   Partially buried   Pedestal   Wall/Pole Mount, mounting kit included
<b>Network Area Type</b>	Drop
<b>Port Type</b>	LC/APC
<b>Port, quantity</b>	2
<b>Splice Tray Included, quantity</b>	1

# SRC3-U4K2B1BE000

---

<b>Splice Tray Type Included</b>	12-way, heat shrink
<b>Splicing Capacity, maximum</b>	12
<b>Splicing Capacity, Single Fusion, maximum</b>	12
<b>Splicing Type, Supported</b>	Single fusion
<b>Splitter Type</b>	No splitter
<b>Splitter, quantity</b>	0

## Dimensions

<b>Height</b>	267 mm   10.512 in
<b>Width</b>	117 mm   4.606 in
<b>Depth</b>	49 mm   1.929 in
<b>Cable Entry Drop Port Diameter</b>	8 mm (0.31 in) mm

## Ordering Tree

# SRC3-U4K2B1BE000



2 cable attachments are supplied.

Cable retention*	Cable Termination Unit (CTU) options					
A	None	<b>B</b>	<b>C</b>	<b>D</b>	<b>E</b>	<b>F</b>
B	NVX-CR-MC-FT-NN					
C	NVX-CR-MC-RD-NN	<b>NVX-CR-MC-FT-NN</b>	<b>NVX-CR-MC-RD-NN</b>	<b>NVX-CR-SA-SM-NN</b>	<b>NVX-CR-TI-SM-NN</b>	<b>NVX-CR-DU-FL-NN</b>
D	NVX-CR-SA-SM-NN	• Flat cable	• Round cable	• Round cable	• Round cable	• Round cable
E	NVX-CR-TI-SM-NN	• Metal clip	• Metal clip	• Dia up to 8 mm	• Dia up to 8 mm	• Dia up to 6.2 mm
F	NVX-CR-DU-FL-NN	• Range 3 x 5 to 4 x 8 mm	• Range 4 to 6.2 mm	• Strength member	• Aramide yarns	• Aramide yarns
G	4xNVX-CR-MC-FT-NN			• Aramide yarns	• Single layer	• Dual layer
H	4xNVX-CR-MC-RD-NN					• Compact length
I	4xNVX-CR-SA-SM-NN					
J	4xNVX-CR-TI-SM-NN					
K	4xNVX-CR-DU-FL-NN					
L	2xNVX-CR-MC-FT-NN and 2xNVX-CR-MC-RD-NN					

## Material Specifications

**Material Type** Impact-resistant polymer

## Optical Specifications

**Fiber Type** G.657.A1 | G.657.A2 | G.657.B3

## Environmental Specifications

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Environmental Space** Above ground | Below ground | Direct burial

**Qualification Standards** IEC 60529, IP68 + 2 m waterhead | IEC 61753-1, category G

**UV Resistance** UV stabilized

# SRC3-U4K2B1BE000

---

**Water Resistance**

Flash test valve at 2 psi (20 kPa)

## Packaging and Weights

**Packaging quantity**

1

**Packaging Type**

Box | Carton

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system



## Included Products

NVX-CR-TI-SM-NN

- NOVUX™ Cable Termination Unit (CTU) for round cables up to 8 mm diameter, with aramide yarns, single layer