



Outdoor Outlet Cover, single gang, universal, two ports

Product Classification

Regional Availability	Asia EMEA Latin America North America
Portfolio	CommScope®
Product Type	Box

General Specifications

Application	Used with KJ Series outlets with adapter Used with M Series modular information outlet Used with SL Series outlets
Color	Clear
Outlet Orientation	Angled
Port Marking Type	Label
Total Ports, quantity	2

Dimensions

Height	150 mm 5.906 in
Width	95.6 mm 3.764 in
Depth	55 mm 2.165 in

Material Specifications

Material Type	Flame/UV-resistant plastic for enclosure and cover
----------------------	--

Environmental Specifications

Operating Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Environmental Space	Indoor/Outdoor
Qualification Standards	IEC 60529, IP67

Packaging and Weights

Packaging quantity	1
Packaging Type	Box

Weight, net

0.28 kg | 0.617 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

