
BLK-RCT-A12D0



Fiber Optic Ribbon Breakout Kit, 1-12F/ribbon, 240-432F/tube, 11-15 mm central tube outside dia., 12 tubes/leg

Product Classification

Regional AvailabilityLatin America | North AmericaProduct TypeFiber breakout kit, rectangular

Product Series BLK-R

General Specifications

Application For use with ribbon fiber cables

Breakout Legs, quantity 1

Fibers per Ribbon, maximum 12

Fibers per Tube, maximum 672

Tube Type Ribbon central tube

Tubes per Leg, quantity 12

Dimensions

Tube Length 5,001.26 mm | 196.9 in

Central Tube Outer Diameter 11 mm - 15 mm (0.43 in - 0.60 in)

Environmental Specifications

Environmental Space Outdoor

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Page 1 of 2

BLK-RCT-A12D0

ROHS

Compliant Compliant



