SC-DLX-CONV-25

SC to DLX Converter

 Hardened drop cables simplify installation and maintenance by reducing splicing requirements in the distribution portion of the network

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Europe | Latin America | North America

Portfolio CommScope®

Product Type Fiber converter

Product Brand DLX®
Product Series FHD

Optical Specifications

Insertion Loss, maximum 0.5 dB **Return Loss, minimum** 65 dB

Environmental Specifications

Operating Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Qualification Standards Telcordia GR-326-CORE

Packaging and Weights

Packaging quantity 25

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



