

# 760242098 | OCM8-SP11GLLG-40DB



OCM8 Fiber Optic Splitter Module, Planar, 1x16 Splitter, singlemode, LC/APC, symmetrical split ratio, 4 m pigtails

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   China   EMEA   India   Latin America   North America
<b>Product Type</b>	Splitter module
<b>Product Series</b>	OCM8

## General Specifications

<b>Functionality</b>	Splitting
<b>Technology Type</b>	Planar lightwave circuit (PLC)
<b>Distribution Type</b>	1 x 16 splitter
<b>Interface, Input</b>	LC
<b>Interface, Output</b>	LC
<b>Interface Feature, Output</b>	APC
<b>Split Ratio</b>	Symmetrical
<b>Splitter, quantity</b>	1

## Dimensions

<b>Height</b>	10 mm   0.394 in
<b>Depth</b>	45 mm   1.772 in
<b>Length</b>	100 mm   3.937 in
<b>Pigtail Length, Input</b>	4 m   13.123 ft
<b>Pigtail Length, Output</b>	4 m   13.123 ft
<b>Pigtail Diameter, Input</b>	1.8 mm   0.071 in
<b>Pigtail Diameter, Output</b>	1.8 mm   0.071 in

## Optical Specifications

<b>Fiber Type</b>	G.657.A1
<b>Directivity, minimum</b>	55 dB
<b>Polarization Dependent Loss, maximum</b>	0.3 dB
<b>Uniformity, maximum</b>	1.55 dB

# 760242098 | OCM8-SP11GLLG-40DB

---

<b>Wavelength Range</b>	1260–1650 nm
<b>Insertion Loss, Splitter, maximum</b>	14.2 dB
<b>Return Loss, Connector, minimum</b>	55 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
------------------------------	--------------------------------------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---