

F4R-HMHM-P

Base Product



HELIAX® 1/2" Superflexible SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male

Product Classification

Product Type	Wireless transmission cable assembly
Product Brand	HELIAX® SureFlex®
Product Series	RSJ4-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	4.3-10 Male
Specification Sheet Revision Level	A

Dimensions

Nominal Size	1/2 in
---------------------	--------

Electrical Specifications

3rd Order IMD	-116 dBm
3rd Order IMD Dynamic Test Method	Two +43 dBm carriers
DTF, Connector A	-32 dB
DTF, Connector B	-32 dB

Environmental Specifications

EN50575 CPR Cable EuroClass Fire Performance	B2ca
EN50575 CPR Cable EuroClass Smoke Rating	s1a

F4R-HMHM-P

EN50575 CPR Cable EuroClass Droplets Rating

d1

EN50575 CPR Cable EuroClass Acidity Rating

a1

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition