

SF-10245NNNNXABB | FBT 1X2 55/45 250UM NO CONN



FBT Coupler, singlemode, 1x2 FBT, 55/45 split ratio, 0.250 mm cable, no connectors

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | EMEA | India | Latin America | North America

Product Type

Bare splitter

General Specifications

Device Type

Component, tubular

Functionality

Splitting

Technology Type

Fused biconic tapered

Distribution Type

1 x 2 splitter

Interface, Input

Stub tail

Interface, Output

Stub tail

Split Ratio

55/45

Splitter, quantity

1

Dimensions

Height

3.2 mm | 0.126 in

Length

55 mm | 2.165 in

Pigtail Length, Input

2.5 m | 8.202 ft

Pigtail Length, Output

2.5 m | 8.202 ft

Pigtail Diameter, Input

0.25 mm | 0.01 in

Pigtail Diameter, Output

0.25 mm | 0.01 in

Optical Specifications

Fiber Type

G.657.A1

Directivity, minimum

55 dB

Polarization Dependent Loss, maximum

0.2 dB

SF-10245NNNNXABB | FBT 1X2 55/45 250UM NO CONN

Wavelength Range	1260–1360 nm 1420–1625 nm
Insertion Loss, Primary Output, maximum	3.2 dB
Insertion Loss, Secondary Output, maximum	4.1 dB
Return Loss, Splitter, minimum	55 dB

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	5%–95%, non-condensing

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

